



TECHNICAL INFORMATION SHEET

NCP-180-A Special Pellistor Gas Sensor For the Detection of Acetylene

Nemoto Sensor
Engineering Co., Ltd.
4-10-9, Takaido-higashi,
Suginami-ku, Tokyo,
JAPAN


General Description

The Nemoto NCP-180-A is a special application catalytic (pellistor) type flammable gas sensor supplied as a matched pair of elements mounted on TO4 size headers and protected by a metal can.

The sensor is specifically designed for the detection of Acetylene in air in the range 0-100% LEL.

Until now, the use of pellistors to monitor Acetylene levels has presented technical problems due to Acetylene's ability to poison catalytic gas sensors, resulting in short sensor lifetimes in the field. The NCP-180-A pellistor, however, cannot be poisoned by Acetylene, and will operate reliably in this application. The NCP-180-A should not be used for any other purpose without first consulting Nemoto.

The device is compatible with a wide range of commercially available Gas Detection Systems and remote flammable gas detection heads.




Specifications:

| | |
|---------------------------------|--------------------------------|
| Recommended Voltage: | 2.0V +/- 0.1V |
| Current Drawn: | 145 +/- 15mA |
| Zero Offset: | 0mV +/- 25mV |
| Minimum Sensitivity: | 8mV / 10% LEL Acetylene in Air |
| Range: | 0-100% LEL |
| Accuracy: | +/- 1%LEL(CH4) |
| Maximum Long Term Drift: | |
| Span: | < +/- 1% Signal/Month |
| Zero: | < +/- 1/2 % LEL/Month |
| Response Time: | T50: 3 sec T90: 8 sec |
| Temperature Range: | -20°C to +60°C |
| Temperature Drift: | (-20°C to +60°C): < +/- 2%LEL |
| Humidity: | 0-100%RH, non-condensing |
| Humidity Response: | +/- 1%LEL |
| Linearity: | Effectively Linear to 100%LEL |

Recommended Circuit:

Note: The value R1 is arbitrary, since the function of R1 is to balance the bridge. 1K is suggested.



Test data on drift, poisoning, temperature performance, linearity are available on the Characterisation Document.

Nemoto has a policy of continuous development and improvement of its products. As such the specification for the device outlined in the data sheet may be changed without notice

ncp-180-a.ppp, issue 3, August 2015

Contact Information:

Europe & Africa Area
Asia Area
Americas Area

Website

www.nemoto.eu
www.nemoto.co.jp
www.nemoto.eu

email


eusensor@nemoto.co.jp
sensor2@nemoto.co.jp
nasensor@nemoto.co.jp

Telephone

+44 (0)1799 543968
+81 3 3333 2760
+1 604 761 7363



Drawing and Dimensions



(± 0.2)

Test data on drift, poisoning, temperature performance, linearity are available on the Characterisation Document.

Nemoto has a policy of continuous development and improvement of its products. As such the specification for the device outlined in the data sheet may be changed without notice

nep-180-a.ppp, issue 3, August 2015

Contact Information:

Europe & Africa Area

Asia Area

Americas Area

Website

www.nemoto.eu

www.nemoto.co.jp

www.nemoto.eu

email

eusensor@nemoto.co.jp

sensor2@nemoto.co.jp

nasensor@nemoto.co.jp

Telephone

+44 (0)1799 543968

+81 3 3333 2760

+1 604 761 7363